

Advanced Photonix (Luna

**Optoelectronics)**

## PDV-V400-46

Gawo la Nambala:  
 Wopanga / Chinthu:  
 Mafotokozedwe Akatundu  
 Datasheets:  
 Mkhalidwe wa RoHS  
 Zolemba  
 Chombo Chochokera  
 Njira Yoperekerana

PDV-V400-46  
 Advanced Photonix (Luna Optoelectronics)  
 PHOTODIODE 550NM 2.98MM SQ TO-46  
 PDV-V400-46.pdf  
 Ili ndi kutsogolera / RoHS yosagwirizana  
 4162 pcs stock  
 Hong Kong  
 DHL/Fedex/TNT/UPS/EMS

PEMPHO LA QUOTATION

Chithunzi chingakhale choyimira. Onani ndondomeko zogwiritsira ntchito mankhwala.

### Mafotokozedwe a PDV-V400-46

GAWO LA NAMBALA	PDV-V400-46
WOPANGA	Advanced Photonix (Luna Optoelectronics)
KUFOTOKOZERA	PHOTODIODE 550NM 2.98MM SQ TO-46
MKHALIDWE WOPANDA UFULU / MKHALIDWE WA ROHS	Ili ndi kutsogolera / RoHS yosagwirizana
CHIWERENGERO CHIPEZEKA	4162 pcs
TSAMBA LAZAMBIRI	PDV-V400-46.pdf
WAVELENGTH	525nm
VOLTAGE - DC ZOSINTHA (VR) (MAX)	75V
KUWONA ANGLE	-
CHIWONETSERO	-
MNDANDANDA	-
KUYANKHA @ NM	-
NTHAWI YOYANKHA	450ns
KUPAKA	Bulk
PHUKUSI / MLANDUWU	TO-46-2 Lens Top Metal Can
MAINA ENA	PT-PDV-V400-46
KUTENTHA KWAMBIRI	-15°C ~ 70°C
MTUNDU WOKWERA	Through Hole
MPHUNO YOPANDA CHISOKONEZO (MSL)	1 (Unlimited)
MKHALIDWE WOPANDA UFULU / MKHALIDWE WA ROHS	Contains lead / RoHS non-compliant
MTUNDU WA DIODE	PIN
KUFOTOKOZEDWA KWAMBIRI	Photodiode 525nm 450ns TO-46-2 Lens Top Metal Can
ZAMAKONO - MDIMA (CHIDA)	150pA
MTUNDU - WAKULIMBITSA	-
MALO OGWIRA NTCHITO	3.089mm <sup>2</sup>

### Matanthauzo okhudzana

Advanced Photonix (Luna Optoelectronics) PDV-V400-46	AAAA Distributor	PDV-V400-46 Wopereka
PDV-V400-46 Mtengo	PDV-V400-46 Zithunzi	PDV-V400-46 Image
PDV-V400-46 PDF Datasheet	PDV-V400-46 Dinani Datasheet	PDV-V400-46 Datasheet
PDV-V400-46 Stock	Gulani PDV-V400-46	Gulani Advanced Photonix (Luna Optoelectronics) PDV-V400-46
Advanced Photonix (Luna Optoelectronics) PDV-V400-46	Advanced Photonix (Luna Optoelectronics) Wogulitsa	Advanced Photonix (Luna Optoelectronics) Distributor
Advanced Photonix (Luna Optoelectronics) PDV-V400-46	Advanced Photonix Inc PDV-V400-46	Advanced Photonix (Luna Optoelectronics) PDV-V400-46
Luna Optoelectronics PDV-V400-46		

### Zogwirizana

<div style="display: flex; align-items: center;"> <div> <p><b>PDV-V404-46</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTODIODE 550NM 2.98MM SQ TO-46                  Zilipo: 6626 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>PDV-P9008</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTOCCELL 10K-200K OHM 4.20MM                  Zilipo: 59915 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p><b>PDV-V403</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTODIODE 600NM 17.74MM SQ TO-5                  Zilipo: 4451 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>PDV-V400</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTODIODE 17.74MM SQ TO-5                  Zilipo: 4861 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p><b>PDV-P9007</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTOCCELL 10K-100K OHM 4.20MM                  Zilipo: 54770 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>PDV-P9200</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTOCCELL 10K-50K OHM 4.20MM                  Zilipo: 47808 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p><b>PDV-V404</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTODIODE 550NM 17.74MM SQ TO-5                  Zilipo: 5325 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>PDV-V405-46</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTODIODE 500NM 2.98MM SQ TO-46                  Zilipo: 6307 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p><b>PDV-V403-46</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTODIODE 600NM 2.98MM SQ TO-46                  Zilipo: 3403 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>PDV-V405</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTODIODE 500NM 17.74MM SQ TO-5                  Zilipo: 4461 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p><b>PDV-P9203</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTOCCELL 10K-30K OHM 4.20MM                  Zilipo: 61559 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p><b>PDV-P9103</b></p> <p>Opanga: Advanced Photonix (Luna Optoelectronics)                  Kufotokozera: PHOTOCCELL 20K-45K OHM 4.20MM                  Zilipo: 55028 pcs</p> <p style="text-align: center; background-color: #eee; padding: 2px; font-weight: bold;">RFQ</p> </div> </div>